



On Line Catalog



BURNDY Catalog Number

YAZ262TC14

UPC Number

7818102278311

Description

CULUG-2/0STR-LONG

Status

W/PORT,2HOLE 1/4STUD

Active

Web Use

BURNDY Product Line

Dimensional

Tongue Angle Straight
Length (in) 3.20
Tongue Type Standard
Height (in) 0.56
Barrell Style Skived
Bolt Hole Size (in) 0.27
Barrel Type Long
Thickness 0.12
B Length (in) 1.50
Pad Width (in) 0.83
E - in 0.62
Strip Length 1-9/16

General

Number of Holes 2
Product Description Copper Compression Lug, 2 Hole w/ Inspection Window, 2/0 AWG, 1/4" Stud, 5/8" Stud Hole Spacing, Long Barrel, Tin Plated

Conductor(s)

Copper Solid Size (Range) 2/0 AWG
Navy Cable Size (Range) 125 (61) Navy
Copper Stranded (Range) 2/0 AWG

Physical

Type of Plating Tin - Electro Plated
Bolt Hole Size 1/4
Color Code Black
Plated (Yes or No) Y
Index Number 13
Product Material Copper

Approvals / Certifications

UL Listed Y
CSA Certified Y
ROHS Compatible Compliant
UL Recognized N
CULUS N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

BURNDY Technical Services

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175

5/30/2018

Datasheet - Burndy - YAZ262TC14

47 East Industrial Park Drive
Manchester NH 03109

47 East Industrial Park Drive
Manchester NH 03109