



BURNDY Catalog Number
UPC Number

Description
Status

Web Use
BURNDY Product Line

YAZ26TC38
7818102399711
CULUG-2/0AWG-LONG W/PORT-
3/8" STUD
Active

Dimensional

Tongue Angle
Length (in)
Barrell Style
Bolt Hole Size (in)
Barrel Type
Thickness
B Length (in)
Pad Width (in)
Strip Length

Straight
2.75
Skived
0.39
Long
0.12
1.50
0.83
1-9/16

General

Number of Holes

Product Description

1
Cu Tubing Hylug (One Hole Code),
1 Hole with Inspection Window,
2/0 AWG Code, 125 Navy, 600V-
35kV, 3/8" stud, Long,
Compression, 0.40 in BCD, Black

Conductor(s)

Copper Solid Size (Range)
Navy Cable Size (Range)
Copper Stranded (Range)

N/A
125 (61) Navy
2/0 AWG

Physical

Type of Plating
Bolt Hole Size
Color Code
Plated (Yes or No)
Index Number
Product Material

Tin - Electro Plated
3/8
Black
Y
13
Copper

Approvals / Certifications

UL Listed
CSA Certified
ROHS Compatible
UL Recognized
CULUS

Y
Y
Compliant
N
N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175