



BURNDY Catalog Number
UPC Number

Description
Status

Web Use
BURNDY Product Line

YAZV262TC14FX
7818102284499
CULUG-2/0FLX-LONG W/PORT,
2HOLE,1/4STUD
Active

Dimensional

Tongue Angle
Strip Length
Length (in)
Barrell Style
Bolt Hole Size (in)
Barrel Type
Thickness
B Length (in)
Pad Width (in)
E - in

Straight
1-9/16
3.20
Chamfered,Skived
0.27
Long
0.13
1.50
0.93
0.62

General

Number of Holes

Product Description

2
Cu Comp Terminal Flex Cond, 2
Hole/W/InspWindow, 2/0
Weld,2/0(325/#24)DLO Flex, 1/0
AWG Code, 600 V-35 kV, 1/4"
Stud, 0.62" Spacing, Lng bbl,
Black, 13 Index

Conductor(s)

Copper Solid Size (Range)
Navy Cable Size (Range)
Copper Stranded (Range)

N/A
N/A
2/0 AWG

Physical

Type of Plating
Bolt Hole Size
Color Code
Plated (Yes or No)
Index Number
Product Material

Tin
1/4
Black
Y
13
Copper

Approvals / Certifications

UL Listed
CSA Certified
ROHS Compatible
UL Recognized
CULUS

Y
Y
Compliant
N
N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175