



BURNDY Catalog Number
UPC Number

Description
Status

Web Use
BURNDY Product Line

YAZV28TC12FX
7818102417077
CULUG-4/0FLX-LONG W/PORT-
1/2" STUD
Active

Dimensional

Tongue Angle	Straight
Strip Length	1-11/16
Length (in)	3.26
Barrell Style	Skived
Bolt Hole Size (in)	0.52
Barrel Type	Long
Thickness	0.14
B Length (in)	1.62
Pad Width (in)	1.14

General

Number of Holes	1
Product Description	Cu Comp Terminal Flex Cond, Bvl Entry, 1 Hole/w/InspWindow, 4/0 Weld, 4/0(550/#24)DLO Flex, 4/0 AWG Code, 600 V-35 kV, 1/2" Stud, Lng bbl, Purple, 15 Index

Conductor(s)

Copper Solid Size (Range)	N/A
Navy Cable Size (Range)	N/A
Copper Stranded (Range)	4/0 AWG

Physical

Type of Plating	Tin
Bolt Hole Size	1/2
Color Code	Purple
Plated (Yes or No)	Y
Index Number	15
Product Material	Copper

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175