



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

YA44L2NT38FX  
 7818100214222  
 CULUG-750FX-3/8X1-NARTNG  
 Active

**Web Use**  
 BURNDY Product Line

Dimensional	
Tongue Angle	Straight
Length (in)	4.74
Tongue Type	Standard
Barrell Style	Chamfered
Bolt Hole Size (in)	0.39
Barrel Type	Standard
Thickness	0.33
B Length (in)	1.65
Pad Width (in)	1.63
E - in	1.00
Strip Length	1-5/8
General	
Number of Holes	2
Product Description	Copper Compression Lug, Narrow Tongue, 2 Hole w/ Inspection Window, 777.7 Flex, 3/8" Stud, 1" Stud Hole Spacing, Short Barrel, Tin - Electro Plated
Conductor(s)	
Flex (Class G) Size - Range	750
Flex (Class H) Size - Range	750
Flex (Class I) Size - Range	750
Copper Solid Size (Range)	N/A
DLO Size (Range)	777.7 (1925/#24)
Copper Stranded (Range)	750
Physical	
Type of Plating	Tin - Electro Plated
Bolt Hole Size	3/8
Color Code	Yellow
Plated (Yes or No)	Y
Index Number	L115
Product Material	Copper
Approvals / Certifications	
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Documentation	

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175