



BURNDY Catalog Number
UPC Number

Description
Status

Web Use
BURNDY Product Line

YAZ382NNTFX
7818101660866
CU HYLUG 700KCMIL 2HOLE NT
FLEX
Active

Dimensional

Tongue Angle
Strip Length
Length (in)
Barrell Style
Bolt Hole Size (in)
Barrel Type
Thickness
B Length (in)
Pad Width (in)
E - in

Straight
2-7/8
6.72
Skived
0.53
Long
0.27
2.81
1.62
1.75

General

Number of Holes

Product Description

2
Copper Compression Lug, 2 Hole
w/ Inspection Window, 535.3 Flex,
1/2" Stud, 1-3/4" Stud Hole
Spacing, Long Barrel, Tin Plated

Conductor(s)

Copper Solid Size (Range)
Navy Cable Size (Range)
Copper Stranded (Range)

N/A
N/A
500 kcmil

Physical

Type of Plating
Bolt Hole Size
Color Code
Plated (Yes or No)
Index Number
Product Material

Tin - Electro Plated
1/2
Pink
Y
L99
Copper

Approvals / Certifications

UL Listed
CSA Certified
ROHS Compatible
UL Recognized
CULUS

Y
Y
Compliant
N
N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175