



BURNDY Catalog Number YA38L2NTCFX
UPC Number 7818105217244
Description CU HYLUG-500 FLEX-NEMA
Status Active

Web Use
 BURNDY Product Line

| Dimensional | |
|-----------------------------|--|
| Tongue Angle | Straight |
| Length (in) | 5.35 |
| Tongue Type | Standard |
| Barrell Style | Chamfered,Skived |
| Bolt Hole Size (in) | 0.52 |
| Barrel Type | Standard |
| Thickness | 0.27 |
| B Length (in) | 1.45 |
| Pad Width (in) | 1.84 |
| E - in | 1.75 |
| Strip Length | 1-7/16 |
| General | |
| Number of Holes | 2 |
| Product Description | Copper Compression Lug, 2 Hole w/ Inspection Window, 535.3 Flex, 1/2" Stud, 1-3/4" Stud Hole Spacing, Short Barrel, Tin Plated |
| Conductor(s) | |
| Flex (Class G) Size - Range | 500 kcmil |
| Flex (Class H) Size - Range | 500 kcmil |
| Flex (Class I) Size - Range | 500 kcmil |
| Copper Solid Size (Range) | N/A |
| DLO Size (Range) | 535.3 (1325/#24) DLO |
| Copper Stranded (Range) | N/A |
| Physical | |
| Type of Plating | Tin |
| Bolt Hole Size | 1/2 |
| Color Code | Pink |
| Plated (Yes or No) | Y |
| Index Number | L99 |
| Product Material | Copper |
| Approvals / Certifications | |
| UL Listed | Y |
| CSA Certified | Y |
| ROHS Compatible | Compliant |
| UL Recognized | N |
| CULUS | N |
| Documentation | |

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175