



BURNDY Catalog Number
UPC Number

Description

Status

Web Use

BURNDY Product Line

UGSKIT2
7818101752799
UNDERGROUND-DIRECT BURIAL
SPLICE KIT
Active

Length (in)
Hex Size

Dimensional

1.38
Slot

Description

General

Product Description

DIRECT BURIAL SPLICE KIT - UGS
Watertight Underground Splice
Kit, 8-2 AWG, w/ Two Heavy Wall
Heat Shrink Sleeves, Al/Cu Rated

Aluminum Size (Range)
Copper Solid Size (Range)
Copper Stranded (Range)

Conductor(s)

8 AWG-2 AWG
N/A
8 AWG-2 AWG

Screw Type
Type of Plating
Connector Type
Plated (Yes or No)
Product Material

Physical

Allen
Unplated
Splice, Reducer
N
Aluminum

UL Listed
CSA Certified
Rated for Direct Burial
ROHS Compatible
UL Recognized
CULUS
Industry Standards

Approvals / Certifications

Y
Y
Y
Compliant
N
N
UL486D

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175