



BURNDY Catalog Number
UPC Number
Description
Status

YA3CN
 7818100196344
 3 STR CU 1-HOLE LONG 1/2
 Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle Straight
 Length (in) 2.86
 Tongue Type Standard
 Barrell Style Chamfered
 Bolt Hole Size (in) 0.52
 Barrel Type Long
 Thickness 0.12
 B Length (in) 1.25
 Pad Width (in) 0.83
 Strip Length 1-5/16

General

Number of Holes 1
 Product Description Copper Compression Lug, 1 Hole w/o Inspection Window, 3 AWG/2 AWG(Sol), 1/2" Stud, Long Barrel, Electro tin Plated

Conductor(s)

Flex (Class G) Size - Range N/A
 Flex (Class H) Size - Range N/A
 Flex (Class I) Size - Range N/A
 Copper Solid Size (Range) 2 AWG
 DLO Size (Range) N/A
 Copper Stranded (Range) 3 AWG

Physical

Type of Plating Tin - Electro Plated
 Bolt Hole Size 1/2
 Color Code White
 Plated (Yes or No) Y
 Index Number 9
 Product Material Copper

Approvals / Certifications

UL Listed Y
 CSA Certified Y
 ROHS Compatible Compliant
 UL Recognized N
 CULUS N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175