



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

KLU125  
 7818103513900  
 2-1/0 CU LUG B  
 Active

**Web Use**  
 BURNDY Product Line

**Dimensional**

Screw Size	3/8
Length (in)	1.99
Size (Hex) or Size (Bolt)	3/8
Stud Size (in)	1/4
Thickness	0.11
Size (Hex) or Size (Bolt) - in	0.38
B Length (in)	0.63
Pad Width (in)	0.63
N (in)	0.43
Hole Size (in)	0.26
Strip Length	15/16
B Length (Fraction)	46/73

**General**

Product Description	Copper Terminal, Offset Tongue, 1 Hole, 2-1/0 AWG (Str), 1/4" Stud, 1 Screw
---------------------	---

**Conductor(s)**

Copper Solid Size (Range)	N/A
Copper Stranded (Range)	2 AWG-1/0

**Physical**

Screw Type	Slot
Installation Torque	50
Type of Plating	Unplated
Connector Type	Terminal
Plated (Yes or No)	N
Product Material	Copper

**Approvals / Certifications**

Rated for Direct Burial	N
UL Listed	N
CSA Certified	N
ROHS Compatible	Compliant
UL Recognized	N
CULUS	Y
Industry Standards	UL467

**Documentation**

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175