



BURNDY Catalog Number
UPC Number
Description
Status

YA39L2TC38
7818100181322
750MCM 2-H 3/8STUD
Active

Web Use
BURNDY Product Line

Dimensional

Tongue Angle
Length (in)
Tongue Type
Barrell Style
Bolt Hole Size (in)
Barrel Type
Thickness
B Length (in)
Pad Width (in)
E - in
Strip Length

Straight
4.36
Standard
Chamfered, Skived
0.39
Standard
0.27
1.42
1.91
1.00
1-15/16

General

Number of Holes
Product Description

2
Copper Compression Lug, 2 Hole
w/ Inspection Window, 750 kcmil,
3/8" Stud, 1" Stud Hole Spacing,
Short Barrel, Tin Plated

Conductor(s)

Flex (Class G) Size - Range
Flex (Class H) Size - Range
Flex (Class I) Size - Range
Copper Solid Size (Range)
DLO Size (Range)
Copper Stranded (Range)

N/A
N/A
N/A
N/A
N/A
750 kcmil

Physical

Type of Plating
Color Code
Plated (Yes or No)
Index Number
Product Material

Tin - Electro Plated
Black
Y
24
Copper

Approvals / Certifications

UL Listed
CSA Certified
ROHS Compatible
UL Recognized
CULUS
Industry Standards

Y
Y
Compliant
N
N
UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM

Monday - Friday

Phone: 800-346-4175