


BURNDY Catalog Number

KC26B1

UPC Number

7818102561077

Description

2-2/0 STR 1 1/16 POST 1

Status

Active

Web Use

BURNDY Product Line

Dimensional

Stud Length (in)	1-1/16, 1.04
Thread Size	1/2-13
Height (in)	1.38
D or Diameter (Fraction) (in)	1-1/4
Nut Width (Fraction)	1
Nut Width (in)	1.04
D - in	1.25
Body Width (Fraction)	7/8
Body Width (in)	0.88
Height (Fraction) (in)	1-3/8

General

Product Description

Mechanical Grounding Connector,
Cable to Flat, 2-2/0 AWG (Str) / 2-
3/0 AWG (Sol), 1/2" Stud

Conductor(s)

Copper Solid Size (Range)	2 AWG-3/0 AWG
Copper Stranded (Range)	2 AWG-2/0 AWG

Physical

Type of Plating	Unplated
Plated (Yes or No)	N
Product Material	Leaded Bronze Alloy

Approvals / Certifications

Rated for Direct Burial	Y
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Exempt
UL Recognized	N
CULUS	N
Industry Standards	UL467

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175