



BURNDY Catalog Number
UPC Number
Description
Status

KA36U
 7818103702544
 2STR-600 DUAL RATED
 Active

Web Use
 BURNDY Product Line

Dimensional

Width (in)	1.50
Length (in)	3.19
Bolt Hole Size (in)	0.38
Thickness	0.44
D - in	1.72
Pad Width (in)	1.52
N (in)	0.78

General

Number of Conductors	1
Number of Holes	1
Product Description	Aluminum Universal Terminal, 1 Hole, 2 AWG (Str)-600 kcmil, 3/8" Stud, 1 Screw, Al/Cu Rated, Tin Plated

Conductor(s)

Aluminum Size (Range)	2 STR- 600 kcmil
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	2 AWG-600 kcmil

Physical

Installation Torque	500
Type of Plating	Tin
Connector Type	Terminal
Bolt Hole Size	3/8
Plated (Yes or No)	Y
Product Material	Aluminum

Approvals / Certifications

Rated for Direct Burial	N
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Exempt
Industry Standards	UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM

Monday - Friday

Phone: 800-346-4175