



BURNDY Catalog Number
UPC Number
Description
Status

UGSKIT250
7818101752866
UNDERGROUND SPLICE KIT
Active

Web Use
BURNDY Product Line

Length (in)
Hex Size

Dimensional

4.00
5/16

Description

General

DIRECT BURIAL SPLICE KIT - UGS
Watertight Underground Splice
Kit, 1 AWG-250 kcmil, w/ Two
Heavy Wall Heat Shrink Sleeves,
Al/Cu Rated

Product Description

Conductor(s)

Aluminum Size (Range)
Copper Solid Size (Range)
Copper Stranded (Range)

1 AWG-250 kcmil
N/A
1 AWG-250 kcmil

Physical

Screw Type
Type of Plating
Connector Type
Plated (Yes or No)
Product Material

Allen
Unplated
Splice, Reducer
N
Aluminum

Approvals / Certifications

UL Listed
CSA Certified
Rated for Direct Burial
ROHS Compatible
UL Recognized
CULUS
Industry Standards

Y
Y
Y
Compliant
N
N
UL486D

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175