




BURNDY Catalog Number
UPC Number
Description
Status

GAR3905
 7818102340444
 4-4/0 4-5 IPS
 Active

Web Use
 BURNDY Product Line

Dimensional

Width (in) 7.50
 Length (in) 1.75
 Height (in) 7.50
 Size (Hex) or Size (Bolt) 3/8
 Size (Hex) or Size (Bolt) - in 0.38
 B Length (in) 1.75

General

Product Description

Mechanical Grounding Connector,
 Conductor to Water Pipe, 4-4/0
 AWG, 4" - 5" Pipe, 3/8" Stud

Other

Type of U Bolt

422G

Approvals / Certifications

UL Listed Y
 CSA Certified Y
 ROHS Compatible Compliant
 UL Recognized N
 CULUS N
 Industry Standards UL467
 Rated for Direct Burial Y

Conductor(s)

Copper Tube Size (SCH40) - Range 4-5
 Rod Size (Range) N/A
 Copper Solid Size (Range) N/A
 Copper Stranded (Range) 4-4/0
 Rebar Size (Range) N/A

Physical

Type of Hardware Steel - Galvanized
 Installation Torque 200
 Type of Plating Unplated
 Plated (Yes or No) N
 Product Material Copper Alloy

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175