

**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

GAR3907  
7818102340688  
4-4/0, 8 IPS  
Active

**Web Use**  
BURNDY Product Line

**Dimensional**

Width (in) 10.62  
Length (in) 1.75  
Height (in) 10.00  
Size (Hex) or Size (Bolt) 3/8  
Size (Hex) or Size (Bolt) - in 0.38  
B Length (in) 1.75

**General**

Product Description

Mechanical Grounding Connector,  
Conductor to Water Pipe, 4-4/0  
AWG, 8" Pipe, 3/8" Stud

**Other**

Type of U Bolt

1028G

**Approvals / Certifications**

UL Listed Y  
CSA Certified Y  
ROHS Compatible Compliant  
UL Recognized N  
CULUS N  
Industry Standards UL467  
Rated for Direct Burial Y

**Conductor(s)**

Copper Tube Size (SCH40) - Range 8  
Rod Size (Range) N/A  
Copper Solid Size (Range) N/A  
Copper Stranded (Range) 4-4/0  
Rebar Size (Range) N/A

**Physical**

Type of Hardware Steel - Galvanized  
Installation Torque 200  
Type of Plating Unplated  
Plated (Yes or No) N  
Product Material Copper Alloy

**Documentation**

**For further technical assistance, please contact us**

**BURNDY LLC - USA**

47 East Industrial Park Drive  
Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
Monday - Friday  
Phone: 800-346-4175

