



BURNDY Catalog Number
UPC Number
Description
Status

GAR3908
 7818102340755
 4-4/0, 10 IPS
 Active

Web Use
 BURNDY Product Line

Dimensional

Width (in)	12.75
Length (in)	1.75
Height (in)	12.00
Size (Hex) or Size (Bolt)	3/8
Size (Hex) or Size (Bolt) - in	0.38
B Length (in)	1.75

General

Product Description	Mechanical Grounding Connector, Conductor to Water Pipe, 4-4/0 AWG, 10" Pipe, 3/8" Stud
---------------------	---

Other

Type of U Bolt	1029G
----------------	-------

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL467
Rated for Direct Burial	Y

Conductor(s)

Copper Tube Size (SCH40) - Range	10
Rod Size (Range)	N/A
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	4-4/0
Rebar Size (Range)	N/A

Physical

Type of Hardware	Steel - Galvanized
Installation Torque	200
Type of Plating	Unplated
Plated (Yes or No)	N
Product Material	Copper Alloy

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175