



BURNDY Catalog Number
UPC Number
Description
Status

YA28LBOX
 7818105541044
 4/0 CU 1-HOLE SHORT 1/2
 Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle	Straight
Length (in)	2.46
Tongue Type	Standard
Barrell Style	Chamfered,Skived
Bolt Hole Size (in)	0.52
Barrel Type	Standard
Thickness	0.14
B Length (in)	0.88
Pad Width (in)	1.02
Strip Length	1-1/8

General

Number of Holes	1
Product Description	Copper Compression Lug, 1 Hole w/ Inspection Window, 4/0 AWG, 1/2" Stud, Short Barrel, Tin Plated

Conductor(s)

Flex (Class G) Size - Range	N/A
Flex (Class H) Size - Range	N/A
Flex (Class I) Size - Range	N/A
Copper Solid Size (Range)	N/A
DLO Size (Range)	N/A
Copper Stranded (Range)	4/0 AWG

Physical

Type of Plating	Tin - Electro Plated
Bolt Hole Size	1/2
Color Code	Purple
Plated (Yes or No)	Y
Index Number	15
Product Material	Copper

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175