



BURNDY Catalog Number
UPC Number
Description
Status

YA39L2NT38
 7818105036388
 CU HYDENT 750 NARROW TON
 Active

Web Use
 BURNDY Product Line

Dimensional	
Tongue Angle	Straight
Length (in)	4.34
Tongue Type	Standard
Barrell Style	Chamfered,Skived
Bolt Hole Size (in)	0.39
Barrel Type	Standard
Thickness	0.27
B Length (in)	1.42
Pad Width (in)	1.63
E - in	1.00
Strip Length	1-1/2
General	
Number of Holes	2
Product Description	Code Conductor Standard Barrel Narrow, 750 kcmil, 3/8 in, 4.34 in L
Conductor(s)	
Flex (Class G) Size - Range	N/A
Flex (Class H) Size - Range	N/A
Flex (Class I) Size - Range	N/A
Copper Solid Size (Range)	N/A
DLO Size (Range)	N/A
Copper Stranded (Range)	750 kcmil
Physical	
Type of Plating	Tin - Electro Plated
Color Code	Black
Plated (Yes or No)	Y
Index Number	24
Product Material	Copper
Approvals / Certifications	
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175