



BURNDY Catalog Number
UPC Number
Description
Status

YAV8CLBOX
 7818105411044
 RING TERMINAL-#8 AWG-UNIN
 Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle	Straight
Length (in)	1.15
Tongue Type	Ring
Stud Size (in)	#10,#8
Pad Width (in)	0.41
Strip Length	1/2"

General

Product Description

Copper Compression Lug, Heavy Duty, Ring Tongue, 1 Hole w/ Inspection Window, AN 8 Flex, #8 - #10 Stud, Short Barrel, Tin Plated

Other

Installation Tooling

Non-Ratchet:MY29-11
 Ratchet:MR4C, MR8-9Q, Y8MRB-1, M8ND w/ N8CT Die Set
 YAV8CL

Bulk Package

Approvals / Certifications

UL Listed
 CSA Certified
 ROHS Compatible
 UL Recognized
 Mil-Spec Class Code
 CULUS
 Industry Standards

Y
 Y
 Compliant
 N
 Class 1
 N
 UL467, Military Specified (Mil-Spec)

Conductor(s)

Aircraft Cable Size (Range)
 Copper Solid Size (Range)
 Navy Cable Size (Range)
 Copper Stranded (Range)

AN 8
 N/A
 N/A
 9-8

Physical

Type of Plating
 Connector Type
 Plated (Yes or No)

Tin - Electro Plated
 Terminal - Ring
 Y

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175