



BURNDY Catalog Number
UPC Number
Description
Status

YAZ262N
7818102085711
2/0 CU-LONG-OPEN-2 NEMA
Active

Web Use
BURNDY Product Line

Dimensional

Tongue Angle
Length (in)
Barrell Style
Bolt Hole Size (in)
Barrel Type
Thickness
B Length (in)
Pad Width (in)
E - in
Strip Length

Straight
4.95
Skived
0.52
Long
0.12
1.50
0.83
1.75
1-9/16

General

Number of Holes
Product Description

2
Copper Compression Lug, 2 Hole
w/ Inspection Window, 2/0 AWG,
1/2" Stud, 1-3/4" Stud Hole
Spacing, Long Barrel, Tin Plated

Conductor(s)

Copper Solid Size (Range)
Navy Cable Size (Range)
Copper Stranded (Range)

N/A
125 (61) Navy
2/0 AWG

Physical

Type of Plating
Bolt Hole Size
Color Code
Plated (Yes or No)
Index Number
Product Material

Tin - Electro Plated
1/2
Black
Y
13
Copper

Approvals / Certifications

UL Listed
CSA Certified
ROHS Compatible
UL Recognized
CULUS
Industry Standards

Y
Y
Compliant
N
N
UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175