



BURNDY Catalog Number
UPC Number
Description
Status

YS31A1
7818107574999
BUTT SPLICE, 4.04 IN L
Active

Web Use
BURNDY Product Line

Strip Length
Barrell Style
Barrel Type

Dimensional

2-1/8
Chamfered
Standard

General

Aluminum Compression Splice,
350 kcmil, 4.04" Splice Length,
Long Barrel, Belled End, Tin Plated

Product Description

Conductor(s)

Aluminum Size (Range)
Copper Stranded (Range)

350 kcmil
350 kcmil

Index Number

Physical

299

Approvals / Certifications

UL Listed
CSA Certified
ROHS Compatible
UL Recognized
CULUS
Industry Standards

Y
Y
Compliant
N
N
UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175