



## NPC06SZDB-WT020M

**NPC RJ45 Patch Cord, category 6, Shielded, LSZH, White, 20 m**

- High-performance patch cords exceeding industry standards supporting NETCONNECT channel specifications
- Standardized transparent, slim-line boots provides consistent patch cord appearance and supports highest density applications
- Colored clips are available to fit the transparent boot, eliminating the need of multiple colors for matching every jacket color
- Colored pull latch tabs are available for easier plug release handling from the modular jack

### Product Classification

|                       |                         |
|-----------------------|-------------------------|
| Portfolio             | NETCONNECT®             |
| Product Series        | NPC                     |
| Product Type          | Twisted pair patch cord |
| Regional Availability | Asia   EMEA             |

### Dimensions

|                      |      |
|----------------------|------|
| Cord Length          | 20 m |
| Diameter Over Jacket | 6 mm |

### Electrical Specifications

|                   |   |
|-------------------|---|
| ANSI/TIA Category | 6 |
|-------------------|---|

### Environmental Specifications

|                       |                                     |
|-----------------------|-------------------------------------|
| Environmental Space   | Low Smoke Zero Halogen (LSZH)       |
| Operating Temperature | -20 °C to +60 °C (-4 °F to +140 °F) |
| Safety Standard       | UL 1863                             |

### General Specifications

|                                |                  |
|--------------------------------|------------------|
| Cable Type                     | S/FTP (shielded) |
| Interface, connector A         | RJ45 plug        |
| Interface, connector B         | RJ45 plug        |
| Jacket Color                   | White            |
| Interface Feature, connector A | Standard         |
| Interface Feature, connector B | Standard         |
| Package Quantity               | 1                |
| Pairs, quantity                | 4                |

### Mechanical Specifications

|                              |           |
|------------------------------|-----------|
| Conductor Type               | Stranded  |
| Conductor Gauge, stranded    | 26 AWG    |
| Plug Insertion Life, minimum | 750 times |

NPC06SZDB-WT020M

Wiring

T568B

## Regulatory Compliance/Certifications

---

**Agency**

RoHS 2011/65/EU

**Classification**

Compliant