



## NPC6AUZDB-BL001M

**NPC RJ45 Patch Cord, category 6A, Unshielded, LSZH, Blue, 1 m**

- High-performance patch cords exceeding industry standards supporting NETCONNECT channel specifications
- Standardized transparent, slim-line boots provides consistent patch cord appearance and supports highest density applications
- Colored clips are available to fit the transparent boot, eliminating the need of multiple colors for matching every jacket color
- Colored pull latch tabs are available for easier plug release handling from the modular jack

## Product Classification

Portfolio	NETCONNECT®
Product Series	NPC
Product Type	Twisted pair patch cord
Regional Availability	EMEA

## Dimensions

Cord Length	1.00 m   3.28 ft
Diameter Over Jacket	7.24 mm   0.29 in

## Electrical Specifications

ANSI/TIA Category	6A
-------------------	----

## Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Safety Standard	UL 1863

## General Specifications

Cable Type	U/UTP (unshielded)
Interface, connector A	RJ45 plug
Interface, connector B	RJ45 plug
Jacket Color	Blue
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard
Package Quantity	1
Pairs, quantity	4

## Mechanical Specifications

Conductor Type	Solid
Conductor Gauge, solid	24 AWG
Plug Insertion Life, minimum	750 times

NPC6AUZDB-BL001M

Wiring

T568B

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU

### Classification

Compliant