



NPC6ASZDB-WT003M

NPC RJ45 Patch Cord, category 6A, S/FTP, LSZH, 3 m, white

- High-performance patch cords exceeding industry standards supporting NETCONNECT channel specifications
- Standardized transparent, slim-line boots provides consistent patch cord appearance and supports highest density applications
- Colored clips are available to fit the transparent boot, eliminating the need of multiple colors for matching every jacket color
- Colored pull latch tabs are available for easier plug release handling from the modular jack

Product Classification

Portfolio	NETCONNECT®
Product Series	NPC
Product Type	Twisted pair patch cord
Regional Availability	Asia EMEA Latin America

Dimensions

Cord Length	3 m
Diameter Over Jacket	6 mm

Electrical Specifications

ANSI/TIA Category	6A
-------------------	----

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Safety Standard	UL 1863

General Specifications

Cable Type	S/FTP (shielded)
Interface, connector A	RJ45 plug
Interface, connector B	RJ45 plug
Jacket Color	White
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard
Package Quantity	1
Pairs, quantity	4

Mechanical Specifications

Conductor Type	Stranded
Conductor Gauge, stranded	26 AWG
Plug Insertion Life, minimum	750 times

NPC6ASZDB-WT003M

Wiring

T568B

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant