

M/E-PSW Series

Mini Fast Ethernet Media Converter

10/100Base-TX to 100Base-FX



M/E-PSW-FX-02(SM)

The M/E-PSW Series is a Fast Ethernet stand-alone Mini media converter that provides cost effective, entry-level media conversion between 10/100Base-TX ports and 100Base-FX ports. With its fixed configuration, deployments are just plug-and-play, and with its small size, it is ideal for locations where space is limited. Operating at Layer 2, the data link layer, this converter not only converts copper to fiber, it also provides rate conversion allowing legacy 10Base-T copper devices to connect to 100Base-FX fiber.

Features

- Unit and Port LEDs allow for quick status information
- Auto-Negotiation
- Fixed Full-Duplex on fiber
- Auto-MDI/MDIX
- Automatic Link Restoration
- Far-End-Fault (FEF)
- Connect to legacy network equipment
- Eliminate Collision Domains

Specifications

Standards	IEEE 802.3
Status LEDs	PWR (Power): (below RJ-45) ON = Link; Flashing = Activity FX-Link/Act (Fiber Link/Activity): (Upper Left on RJ-45) ON = Link; Flashing = Activity TX-Link/Act (Copper Link/Activity): (Upper Right on RJ-45) ON = Link; Flashing = Activity
Dimensions	Width: 1.8" [46 mm] Depth: 3.3" [85 mm] Height: 0.85" [22 mm]
Power Consumption	2.6 Watts
Power Supply	External AC/DC required; +12VDC, 0.5A min
Environment	Operating: 0°C to 50°C Storage: -15°C to 65°C Humidity: 5% to 95% (non-condensing) Altitude: 0 – 10,000 ft.
Weight	2 lbs. [0.90 kg]
Compliance	Safety: Wall Mount Power Supply: UL Listed, cUL Listed (Canada) FCC Class A, CISPR22/EN55022 Class A, EN55024, CE Mark
Warranty	Lifetime

Ordering Information

M/E-PSW-FX-02

10/100Base-TX (RJ-45) [100 m/328 ft.]
to 100Base-FX 1300nm multimode (ST)
[2 km/1.2 mi.] Link Budget: 11.0 dB

M/E-PSW-FX-02(SC)

10/100Base-TX (RJ-45) [100 m/328 ft.]
to 100Base-FX 1300nm multimode (SC)
[2 km/1.2 mi.] Link Budget: 11.0 dB

M/E-PSW-FX-02(SM)

10/100Base-TX (RJ-45) [100 m/328 ft.]
to 100Base-FX 1310nm single mode (SC)
[20 km/12.4 mi.] Link Budget: 16.0 dB

Optional Accessories (sold separately)

Wide Input Power Supplies

SPS-2460-SA

Stand-Alone Power Supply

Mounting Options

WMBM

Wall Mount Bracket for Mini

M-MCR-01

18-Slot Powered Mini Chassis

DRBM

DIN Rail Mount Bracket for Mini

RMBM

Rack Mount Bracket for Mini, use with
RMS19-SA4-02 and/or E-MCR-05

Power Supply Included

To order the corresponding country specific power supply, add the extension from the list below to the end of the SKU; Ex: M/E-TX-FX-02-NA

-NA = Country Code

- NA = North America
- LA = Latin America
- EU = Europe
- UK = United Kingdom
- SA = South Africa
- JP = Japan
- OZ = Australia
- BR = Brazil