

AX101554 Connectivity Accessories - LabelFlex Automated Labeling Solution



For more Information
please call

1-800-Belden1

General Description:

LabelFlex for HD-Series Patch Panels, White, 18 labels/sheet, 5 sheets/pack

Usage (Overall)

Related Parts: HD-Series Patch Panels

Physical Characteristics (Connectivity)

Dimensions

Dimensions:

Height (in.)	Width (in.)
11.000	8.500

Materials

Materials:

Description
Label: Card
Thickness: 180gsm
Release Liner: N/A

Color

Color: White

Weight

Weight: 0.100 lbs.

Packaging

Packaging: 5 sheets packaged in a plastic bag.

Mechanical Characteristics (Connectivity)

Storage Temperature Range: -40°C To +70°C

Installation Temperature Range: -10°C To +60°C

Applicable Specifications and Agency Compliance (Overall)

Suitability

Suitability - Indoor: Yes - Indoor

Notes (Overall)

Notes: Actual Label Dimension: 7.34 in. (186.5mm) x 0.47 in. (12mm)

Product Family

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
AX101554	1 EA	0.202 LB			LFLEX HDPP LABELS,WHI

Revision Number: 0 Revision Date: 10-16-2017

© 2017 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale.