



BURNDY Catalog Number
UPC Number
Description
Status

TP148F
 7818107126899
 FORK- 16- 14 AWG- VINYL
 Active

Web Use
 BURNDY Product Line

Dimensional

Max Insulation Diameter	0.18
Length (in)	0.86
Tongue Type	Fork
Thickness	0.03
B Length (in)	0.26
Pad Width (in)	0.31
Strip Length	13/64

Electrical

Max Voltage Rating	600
--------------------	-----

General

Product Description	Copper Terminal, Fork Tongue, 16-14 AWG, #6-#8 Stud, Vinyl Insulated, Tin Plated
---------------------	--

Other

Bulk Package	BA14EF8M
--------------	----------

Physical

Type of Plating	Tin
Connector Type	Terminal - Fork
Color Code	Blue
Insulation Type	Vinyl
Plated (Yes or No)	Y

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N

Conductor(s)

Copper Solid Size (Range)	N/A
Copper Stranded (Range)	16 AWG-14 AWG

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175