
12-FIBER OM4+ M4 CASSETTE WITH 12 LC DUPLEX ADAPTERS TO 1 MPO (M), TIER 2, METHOD B, NEAR END

M4LCD12-50EC2A1 | [Legrand](#)



FEATURES & BENEFITS

Infinium M4 pre-terminated cassettes with method B provide rapid deployment and have a flipped polarity inside the modules, which use key-up to key-up MPO adapters and allows for straight through patching. The rugged metal housing offers additional durability and includes a built-in internal bend limiting feature to assure optimum optical performance.



- **Method B connectivity:** Has flipped polarity and uses key-up to key-up adapters.
- **Pre-terminated solution:** For fastest installation, highest performance and consistent factory quality.
- **Fiber port labeling:** Provides easier administration.
- **Compact high density design:** Made with a rugged metal housing.

SPECIFICATIONS

GENERAL INFO

Category Performance Application: OM4+
Number Of Ports: 12
Typical Applications: Multimode
Connection Type: MPO-LC
Installation Destination: Fiber Cabinets
Product Series: Infinium
Type: High Density Cassettes

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

DIMENSIONS

Depth (US): 4.76"
Height (US): 1.14"

Width (US): 3.45"

CORD INFORMATION

Fiber Type: 50/125 LOMMF

TECHNICAL INFORMATION

Connection Method: Method B

Fiber Capacity: 12

Capacity: High Density

Equipment Type: Pre-Terminated Cassettes

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA