

Jabra Engage 65

Engineered to be the world's most powerful professional wireless headsets*

- Industry-leading wireless performance. Better customer connections.
- Crystal-clear calls. Enhance the customer experience.
- More talk time, less interruptions. Increase productivity.



Specifications



Product name	Engage 65 Stereo	Engage 65 Mono	Engage 65 Convertible
Audio	Speaker size	2pcs Ø 28 x 3.9mm	Ø 28 x 3.9mm
	Speaker Max output power	<118 dBSPL(A)	<118 dBSPL(A)
	Speaker frequency range	40Hz-16kHz	40Hz-16kHz
	Speaker bandwidth music mode	40Hz-16kHz	40Hz-16kHz
	Speaker bandwidth speak mode	150 - 6,800Hz	150 - 6,800Hz
	Microphone type	Dual Microphone - ECM Uni-Directional and Analog MEMS system	Dual Microphone - ECM Uni-Directional and Analog MEMS system
	Microphone frequency range	100Hz-10KHz	100Hz-10KHz
Ease of Use	Certifications	CE, CB, FCC, IC, NOM, NTC, EAC, PSB, ICASA, TELEC, SIRIM, ACMA, NZ Telepermit, UL	
	Intuitive audio control	Answer/end call - reject call - volume control	
	Voice/Mute	Yes	
	Busylight	Integrated red light on the microphone tip and the headset, activated when on a call or manually by the user when busy, to act as a "do not disturb" signal (Convertible model has busylight on earcup only).	
Fit & comfort	Headset form factor	Headband	Headband (neckband as accessory)
	Earhook	N/A	N/A
	EarGel™	N/A	N/A
	Neckband	N/A	Optional
Battery	Talk time (up to / hours) ¹	13	13
	Standby time	52 (improves with use of power nap feature)	52 (improves with use of power nap feature)
	Charging time	90 min	90 min
	AC power supply	Yes	Yes
	Power consumption	7.5V/650mA	7.5V/650mA
	Battery status % after 30 min/60 min	40% after 30 min and 80% after 60 min	40% after 30 min and 80% after 60 min
Connectivity	Connectivity	Desk phone & softphone (PC)	Desk phone & softphone (PC)
	Connection (mini jack, USB, etc)	Micro USB, RJ-9 for handset, RJ-9 for desk phone audio, RJ-45 for AUX	
	DECT device	Yes	Yes
	NFC	No	No
	Bluetooth® device	No	No
	Operating range (up to)	150m/490ft	150m/490ft
	Headset bandwidth	Narrowband and wideband. Optimized for music (when not in call)	Narrowband and wideband. Optimized for music (when not in call)

Specifications



Product name		Engage 65 Stereo	Engage 65 Mono	Engage 65 Convertible
General	Box content	Headset, base, power supply, USB cable, desk phone cable, documentation, Quick start guide	Headset, base, power supply, USB cable, desk phone cable, documentation, Quick start guide	Headset, earhook, base, power supply, USB cable, desk phone cable, documentation, Quick start guide and accessory earhook and eargel
	Packaging dimensions (L x W x H)	Unit box: 147 x 190 x 93mm	Unit box: 147 x 190 x 93mm	Unit box: 145 x 190 x 93mm
	Master carton dimensions (L x W x H)	395 x 300 x 206mm	395 x 300 x 206mm	395 x 300 x 206mm
	Main unit dimension (W x D x H)	Base: 93 x 90 x 106mm Headset: 141 x 32 x 169mm	Base: 93 x 90 x 106mm Headset: 147 x 32 x 169mm	Base: 93 x 90 x 110mm Headset: 105 x 32 x 50mm
	Weight (incl main wearing style)	Base: 203g Headset: 83g	Base: 203g Headset: 57g	Base: 203g Headset: 18g
	Battery included	Yes/exchangeable	Yes/exchangeable	Yes
	Security	DECT Security Step C & using FIPS approved algorithms for key generation, payload encryption and authentication		
	Warranty	North America: 1 year limited warranty Europe/APAC: 2 year limited warranty	North America: 1 year limited warranty Europe/APAC: 2 year limited warranty	North America: 1 year limited warranty Europe/APAC: 2 year limited warranty
	Operating temperature	-10°C to +55°C (non condensing)	-10°C to +55°C (non condensing)	-10°C to +55°C (non condensing)
	Storage temperature	-5°C to +45°C (non condensing)	-5°C to +45°C (non condensing)	-5°C to +45°C (non condensing)
	Charging plug dimensions	Ø 2.35mm	Ø 2.35mm	Ø 2.35mm

Region	SKU	Description	EAN	UPC
EMEA	9553-553-111	Jabra Engage 65 Mono	5706991019681	706487017257
	9555-553-111	Jabra Engage 65 Convertible	5706991019728	706487017295
	9559-553-111	Jabra Engage 65 Stereo	5706991019827	706487017394
NA	9553-553-125	Jabra Engage 65 Mono	5706991019704	706487017271
	9555-553-125	Jabra Engage 65 Convertible	5706991019742	706487017318
	9559-553-125	Jabra Engage 65 Stereo	5706991019841	706487017417
UK/HK/ SG/AU/NZ	9553-553-117	Jabra Engage 65 Mono	5706991019698	706487017264
	9555-553-117	Jabra Engage 65 Convertible	5706991019735	706487017301
	9559-553-117	Jabra Engage 65 Stereo	5706991019834	706487017400
JP	9553-553-136	Jabra Engage 65 Mono	5706991019711	706487017288
	9555-553-136	Jabra Engage 65 Convertible	5706991019759	706487017325

Jabra.com/Engage