



B


A



REAR VIEW



TOP VIEW




FRONT VIEW

1

PANDUIT P/N	WEIGHT
P36G18M	9.9kg

NOTES:

1. IDENTIFICATION:
UNIT TYPE: MONITORED & SWITCHED PER OUTLET
ORIENTATION: VERTICAL, 0U, FULL
OUTLET QTY&TYPE: (30)C13, (6)C19
BREAKER QTY&TYPE: (2) 20AMP, DOUBLE-POLE
INPUT VOLTAGE: 200-240VAC
INPUT CURRENT: 30A (24A DERATED)
INPUT PHASE: SINGLE-PHASE
RATED POWER: 5.0 kVA
INPUT PLUG: NEMA L6-30P
INPUT CORD LENGTH: 3m [10']
2. ACCESSORIES:
POCKET GUIDE
3. RoHS COMPLIANT
4. VISIT PANDUIT'S ON-LINE CATALOG AT WWW.PANDUIT.COM
FOR ADDITIONAL PRODUCT INFORMATION CONTAINED IN THE
SPECIFICATION SHEET AS WELL AS A CURRENT LIST OF
PRODUCTS APPLICABLE FOR USE WITH THIS PART
5. MAXIMUM ALLOWABLE INPUT POWER = 5.0kW
6. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL,
STATE, AND LOCAL CODES



SIDE VIEW

PLUG
30 AMP, 250V
TWIST-LOCK
NEMA L6-30P

SIX(6)
RECEPTACLES
16 AMP, 250V
STRAIGHT BLADE
IEC 60320/C13

THIRTY(30)
RECEPTACLES
10 AMP, 250V
STRAIGHT BLADE
IEC 60320/C13

01A	10/18/2017	WSJ	MIM	EDM	INITIAL RELEASE	P36G18M
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

WE ASK THAT YOU CHECK FULLY THE
DIMENSIONS, NOTES, AND SIGN THE CLIENT
SIGNATURE BOX.
THE JOB WILL NOT PROGRESS WITHOUT
SIGNED APPROVAL. PLEASE DO NOT DELAY
IN RETURNING PROOF AS IT WILL AFFECT
DELIVERY

SIGN
DATE
PRINT

TITLE
INTELLIGENT SERIES PDU
P36G18M
CUSTOMER DRAWING

ITEM REVISION NAME
DATASHEET FILE NAME:

UNLESS OTHERWISE SPECIFIED
DIMENSIONAL TOLERANCE ARE: mm [IN]
Tolerance(mm)
0<L≤50 ±0.5
50<L≤250 ±1.0
250<L≤500 ±1.5
500<L≤1000 ±2.5
1000<L≤2000 ±4.0
THIRD ANGLE
PROJECTION

MATERIAL/COLOR:
N/A
DRAWING NUMBER:
P36G18M_DC

DRAWN BY: WSJ
DATE: 10/18/2017
CHK: SEAN
SCALE: NONE

SHT 1 OF 1

SCALE
B