

Pan-Wrap™ Braided Sleeving

PANDUIT®

SPECIFICATION SHEET

specifications

Braided sleeving shall be designed of thermoplastic polyester halogen-free material for applications that require protection and bundling of wires, cables, hoses, or tubing; especially after cable is routed and terminated and possible re-entry is required (maintenance and repair). Braided sleeving shall be rated for use up to 257°F and provides exceptional flammability performance.



technical information

Material:	Polyethylene Terephthalate (PET)	Flame Retardant (PET)
Operating temperature:	-94°F to 257°F (-70°C to 125°C)	-94°F to 257°F (-70°C to 125°C)
Flammability:	UL 94-V0	UL 1441 VW-1
Recommended cutting tool:	Hot Knife	Hot Knife
Compliance:	Halogen Free RoHS	Halogen Free RoHS

key features and benefits

Split wrap design	Allows for installation after cable routing is complete, breakouts of single and multiple cables, and addition or removal of cables post-installation 25% edge overlap ensures complete coverage without opening
Open weave fabrication	Highly flexible, does not trap heat or humidity; quiet in high vibration applications
Patented installation tool	Allows easy loading of maximum bundle diameters to speed installation

applications

Pan-Wrap™ Braided Sleeving is well suited for the challenging applications found in the transportation and marine industries due to its open weave design, lack of halogens, and exceptional flammability performance. Complicated cable assemblies as well as

dynamic cabling environments also benefit greatly from the split wrap design. The Pan-Wrap™ Installation Tool reduces installation time by allowing easy loading of maximum bundle diameters; especially effective on long runs.

Pan-Wrap™ Braided Sleeving

Polyethylene Terephthalate (PET)

Nominal Size

1/8" (3.2mm):	SE12PS-4CR0
1/4" (6.4mm):	SE25PS-TR0
1/2" (12.7mm):	SE50PS-CLR0
3/4" (19.1mm):	SE75PS-CR0
1" (25.4mm):	SE100PS-CR0
1 1/2" (38.1mm):	SE150PS-LQR0

Flame Retardant

Polyethylene Terephthalate

1/8" (3.2mm):	SE12PSFR-4CR0
1/4" (6.4mm):	SE25PSFR-TR0
1/2" (12.7mm):	SE50PSFR-CLR0
3/4" (19.1mm):	SE75PSFR-CR0
1" (25.4mm):	SE100PSFR-CR0
1 1/2" (38.1mm):	SE150PSFR-LQR0

Related Products

Pan-Wrap™ Installation Tools

Part Number	For use with
PWT38:	SE25PS-TR0 SE25PSFR-TR0
PWT50:	SE50PS-CLR0 SE50PSFR-CLR0
PWT75:	SE75PS-CR0 SE75PSFR-CR0
PWT100:	SE100PS-CR0 SE100PSFR-CR0
PWT150:	SE150PS-LQR0 SE150PSFR-LQR0

Pan-Wrap™ Braided Sleeving

installation instructions using the Pan-Wrap™ installation tool



Open Pan-Wrap™ Tool and insert bundle.



Close tool to contain bundle.



Insert Pan-Wrap™ Braided Sleeving onto end of tool until approximately 3" of it covers the bundle.



Grasp end of Pan-Wrap™ Braided Sleeving and bundle while pulling the tool along the bundle length.

part information

Part Number	Nominal Size Diameter		Length Per Reel		Color	Nominal Wall Thickness		Weight Lbs./100'
	In.	mm	Ft.	m		In.	mm	

Polyethylene Terephthalate (PET)

SE12PS-4CR0	0.125	3.2	400	122.0	Black	0.024	0.6	0.20
SE25PS-TR0	0.25	6.4	200	61.0	Black	0.025	0.6	0.60
SE50PS-CLR0	0.50	12.7	150	45.7	Black	0.025	0.6	1.40
SE75PS-CR0	0.75	19.1	100	30.5	Black	0.025	0.6	1.60
SE100PS-CR0	1.00	25.4	100	30.5	Black	0.038	1.0	2.00
SE150PS-LQR0	1.50	38.1	75	22.9	Black	0.038	1.0	2.70

Flame Retardant Polyethylene Terephthalate

SE12PSFR-4CR0	0.125	3.2	400	122.0	Black	0.024	0.6	0.20
SE25PSFR-TR0	0.25	6.4	200	61.0	Black	0.025	0.6	0.60
SE50PSFR-CLR0	0.50	12.7	150	45.7	Black	0.025	0.6	1.40
SE75PSFR-CR0	0.75	19.1	100	30.5	Black	0.025	0.6	1.60
SE100PSFR-CR0	1.00	25.4	100	30.5	Black	0.038	1.0	2.00
SE150PSFR-LQR0	1.50	38.1	75	22.9	Black	0.038	1.0	2.70

DISCLAIMER: The information contained herein is intended as a guide for use by persons having technical skill at their own discretion and risk. Before using, buyer shall determine the suitability of the Panduit product for his intended use and buyer assumes all risk and liability whatsoever in connection therewith.

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA
Markham, Ontario
cs-cdn@panduit.com
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
cs-emea@panduit.com
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
cs-ap@panduit.com
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
cs-japan@panduit.com
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
cs-la@panduit.com
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
cs-aus@panduit.com
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300

PANDUIT®

©2015 Panduit Corp.
ALL RIGHTS RESERVED.
WASP41--WW-ENG
5/2015