


ALL DESIGN, OPERATIVE AND PROCESS DATA PERTAINING TO THE ARTICLE SHOWN ON THIS SHEET IS THE PROPERTY OF POLYPHASER CORPORATION. THE INFORMATION IS NOT TO BE COPIED, REPRODUCED, REVEALED TO OR APPROPRIATED BY OTHERS WITHOUT THE EXPRESS WRITTEN CONSENT OF POLYPHASER CORPORATION.

These Commodities, or technology are exported from the U.S. in accordance with the Export Administration Regulations. Diversion contrary to U.S. law prohibited.

# REVISIONS

REV LTR	DESCRIPTION	DATE	APPROVAL	Q.A.
B	INC ECN 2227	SH 05/14/04	BL	LJ



ITEM	PART NUMBER	DESCRIPTION	QTY
1	6050-0022-01	WEATHER SEALANT 2.5 X 6	1
2	6060-0118	ROLL BLACK ELEC TAPE	1
3	8100-0144	INS SHEET WK-1	1
4	7030-0009	HEADER CARD	1
5	7020-0772	BARCODE LABEL	1
6	7050-0010	CLEAR POLY BAG 5 x 6 3MIL ROLL	1

## NOTE:

1. PLACE WEATHER SEALANT (ITEM 1) INTO POLYBAG (ITEM 6).
2. PLACE ITEMS 2 AND 3 INTO POLYBAG (ITEM 6).
3. STAPLE HEADER CARD (ITEM 4) TO POLYBAG (ITEM 6).
4. PLACE BARCODE LABEL (ITEM 5) IN APPROXIMATELY SHOWN LOCATION.
5. BAG MUST BE SECURELY SEALED TO PREVENT LOSS OF HARDWARE.
6. WEATHER SEALANT CAN BE IN THE FORM OF ROLL OR STRIP.

### HOLE TOLERANCES UNLESS OTHERWISE SPECIFIED

DIAMETER	TOLERANCE
.013-.039	+.004/-0.001
.040-.129	+.005/-0.001
.130-.250	+.006/-0.001
.251-.485	+.008/-0.001
.486-.735	+.010/-0.001
.736-.985	+.012/-0.001
.986 AND LARGER	±0.010

### TOLERANCES UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [ ] ARE MILLIMETERS ANGLES = ±1° 0' 0" SURFACE FINISH OF 63/or BETTER

INCHES	[MILLIMETERS]
.X = ±.050	[XX. = ±1.27]
.XX = ±.030	[.XX = ±0.76]
.XXX = ±.010	[.XXX = ±0.25]
DO NOT SCALE DRAWING	

DRAFTER	DATE
I. BENNETT	06/23/00
MECH ENGINEER	DATE
R. DUNNING	07/14/00
ELEC ENGINEER	DATE
K. BARTEL	07/13/00
QUALITY DEPT	DATE
R. MATHEUS	07/14/00

<b>PolyPhaser</b>		P.O. BOX 9000 MINDEN, NV 89423 TEL: 775-782-2511 FAX: 775-782-4476	
DWG NO/PART NO/DESCRIPTION		WK-1 TOP PRINT	
CAGE CODE	FILE NAME	SCALE	SHEET
61114	-A1	1/2	1 OF 1