

## 6-LC (12 FIBERS) SINGLE MODE ADAPTERS WITH CERAMIC ALIGNMENT SLEEVES



OR-OFP-LCD12AC | [Ortronics](#)

### FEATURES & BENEFITS

Ortronics fiber adapter panel allows for flexibility and expansion with an industry accepted style. The adapter panel snaps in for installation and can be removed easily for future changes. The adapter panel is silkscreened for easy port identification.



- **Standard adapter panel is front removable:** Ideal for simple moves, adds, and changes
- **Uses plunger/grommet fastener:** Holds adapter panels securely in place

### SPECIFICATIONS

#### GENERAL INFO

Color: Blue  
Number Of Ports: 6  
Typical Applications: Single-mode  
Connection Type: LC  
Installation Destination: Fiber Cabinets

#### ASSEMBLY/INSTALLATION INFORMATION

Mounting Hardware Included: Yes

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

#### DIMENSIONS

Height (Metric): 30 mm  
Height (US): 1.19"

Width (Metric): 130 mm

## TECHNICAL INFORMATION

Fiber Capacity: 12

Performance Rating: LC

Capacity: Standard Density

Equipment Type: Adapters

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

