

## 6-LC (12 FIBERS) MULTIMODE ADAPTERS WITH PHOSPHOR-BRONZE ALIGNMENT SLEEVES



OR-OFP-LCD12MB | [Ortronics](#)

### FEATURES & BENEFITS

Ortronics fiber adapter panel allows for flexibility and expansion with an industry accepted style. The adapter panel snaps in for installation and can be removed easily for future changes. The adapter panel is silkscreened for easy port identification



**PRODUCT**  
ENVIRONMENTAL PROFILE

- **Standard adapter panel is front removable:** Ideal for simple moves, adds, and changes.
- **Uses plunger/grommet fastener:** Holds adapter panels securely in place.

### SPECIFICATIONS

#### GENERAL INFO

Number Of Ports: 6  
Typical Applications: Multimode  
Connection Type: LC  
Installation Destination: Fiber Cabinets

#### ASSEMBLY/INSTALLATION INFORMATION

Mounting Hardware Included: Yes

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

#### DIMENSIONS

Height (Metric): 30 mm

Height (US): 1.19"  
Width (Metric): 130 mm

#### TECHNICAL INFORMATION

Fiber Capacity: 12  
Performance Rating: LC  
Capacity: Standard Density  
Equipment Type: Adapters

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant

