

Recessed Angled Discrete Distribution Module Panel, SL, STP, 1U, 24 port



Product Classification

Portfolio	CommScope®
Product Type	RJ45 patch panel
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Dimensions

Depth, with cable management	137.16 mm 5.40 in
Diameter Over Dielectric, maximum	1.168 mm 0.046 in
Diameter Over Dielectric, minimum	0.762 mm 0.030 in
Height	44.45 mm 1.75 in
Width	482.60 mm 19.00 in

Electrical Specifications

ANSI/TIA Category	6 6A
--------------------------	--------

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cUL RCM UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Total Ports, quantity	24
Cable Type	S/STP (shielded)
Brand	CommScope®
Color	Black
Modules, quantity	0
Package Quantity	1
Rack Type	EIA 19 in
Rack Units	1.0

Mechanical Specifications

Panel Style Angled recessed

Material Type High-impact, flame retardant, thermoplastic | Powder-coated steel

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2008

Classification

Compliant

Designed, manufactured and/or distributed under this quality management system

