LANscape® Fibre Housing, SC UPC

24 Fibres, 1U, Singlemode OS2, universal splice pack, protectors not included, black

CORNING

The LANscape® housing family was designed for various applications in 19-in racks and main distribution frames. The fixed or sliding housings can be equipped with industry common adapter types in different fibre categories and are suitable for direct field termination, fusion splicing with pigtails as well as preterminated solutions. The four back openings accommodate cable glands. Additional brackets for cable strain relief for FTTD/FTTO applications or U-Clips for Plug & Play[™] and EDGE[™] trunks can be mounted at the backside.

The space-optimized interior makes it easy to work with ongoing moves, adds and changes (MACs), thus reducing the risk of network disruptions.

Features and Benefits

Easy to remove top cover No tools needed

Housing made of aluminium Lightweight, but robust

Quick-mount feature Allows single-person mounting of housing

Accomodate different termination methods

Pigtail splicing, field connectorisation, preterminated cables, Plug & Play[™] or EDGE[™] trunks can be installed in the same housing

Low installation depth Mountable in shallow cabinets or racks

Multiple labelling options

Port numbering above and below adapter modules or customised labels

LC Duplex adapter modules with self-closing shutters

Additional protection at no extra cost

Specifications

General Specifications	
Mounting type	Rack 19"
Access type	Front, top, rear
Lockable	Yes
Fibre category	Single-mode (OS2)
Application	Splicing



CORNING

LANscape® Fibre Housing, SC UPC

24 Fibres, 1U, Singlemode OS2, universal splice pack, protectors not included, black

CORNING

Temperature Range		
Operation	-10 °C to 60 °C	
Storage	-10 °C to 60 °C	
Installation and assembly	-10 °C to 60 °C	

Design - Hardware	
Housing material	Aluminum
Housing colour	Black
Height unit	1U
Fibre count	24
Cable entry type	Prepunched circular for cable glands (2 x M20 and 2 x M25 on the rear) $% \left(2 \right) = 0$
Number of adapters	24
Number of pigtails	24
Pigtail length	2 m
Connector type	SC UPC
Number of splice trays	2
Splice tray type	Universal cassette with organisers for heat-shrink and crimp splice protectors
Splice protectors type	Without organizer and protectors
Number of splice protectors	0
Total splice capacity	24
Maximum cable number in basic unit with accessories	4
Additional cable number reacheable with accessories	4

Mechanical Characteristics

Dimensions (HxWxD)

44 mm x 483 mm x 233 mm

Optical Specification - Hardware

Insertion loss, max.

0.25 dB



CORNING

LANscape® Fibre Housing, SC UPC

24 Fibres, 1U, Singlemode OS2, universal splice pack, protectors not included, black

CORNING

Design Adapter	
Adapter type	SC UPC
Adapter housing colour	Blue
Shuttered adapter	No

Ordering Information

Part Number	LAN1-2472-PGTL-B
Product Description	LANscape® Fibre Housing, loaded with SC UPC adapters and pigtails, 24 Fibres, 1U, Singlemode OS2, universal splice pack, protectors not included, black

Shipping Information

Units Per Delivery	1/1
Package Contents	LANscape Fibre Housing with adapters, splice packs including coloured pigtails, 1x M20 cable gland and basic accessories



Corning Optical Communications GmbH & Co. KG · Leipziger Strasse 121 · 10117 Berlin, GERMANY 00 800 2676 4641 · FAX: +49 30 5303 2335 · www.corning.com/opcomm/emea A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2018 Corning Optical Communications. All rights reserved.