



TRACJACK FACEPLATE, STAINLESS STEEL, TWO-PORT (SINGLE GANG)

OR-403STJ12 | [Ortronics](#)

FEATURES & BENEFITS

Ortronics single gang stainless steel faceplate accepts front-loading TracJack modules. TracJacks mount flush with faceplate and includes two snap-in label fields.



- Stainless steel construction
- TracJack mounts flush with faceplate
- Smooth low profile design
- Rear plastic housing
- Recessed label fields
- Accepts front loading snap-in TracJacks
- Front load module approach
- RoHS compliant

SPECIFICATIONS

GENERAL INFO

Color: Stainless steel
Footprint: TracJack
Number Of Ports: 2
Product Series: Clarity
Type: Plates and Boxes

ASSEMBLY/INSTALLATION INFORMATION

Mounting Hardware Included: 6-32 x 1" screws (2 ea)

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: 1
CUL Listing No: E131600

UL Listing No: E131600

UL Standard: Yes

CONSTRUCTION INFORMATION

Component 1: Stainless Steel TracJack Faceplate

Component 2: Plastic Backplate

Component 3: Designation Strip

Component 4: Designation Strip

Component 5: Screw 6-32 x 1" flat head

Finish Plating 1: #5 Brushed

Finish Plating 3: Clear

Finish Plating 4: White

Finish Plating 5: Nickel plating 15u"

Material 1: 20 Gauge Stainless Steel

Material 2: PC/ABS UL94-VO

Material 3: Lexan

Material 4: Paper

Material 5: Cold rolled steel 1010

DIMENSIONS

Depth (Metric): 6.10 mm

Height (Metric): 114.3 mm

Height (US): 4.5"

Width (Metric): 69.85 mm

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: TAIWAN

Buy American Act Status: Trade Agreement Act Compliant