



## TRACJACK FACEPLATE, STAINLESS, FOUR-PORT (SINGLE GANG)

OR-403STJ14 | [Ortronics](#)

### FEATURES & BENEFITS

Ortronics single gang stainless steel faceplate accepts front-loading TracJack modules. TracJacks mount flush with faceplate and includes two snap-in label fields.



**PRODUCT**  
ENVIRONMENTAL PROFILE

- Stainless steel construction
- TracJack mounts flush with faceplate
- Smooth low profile design
- Rear plastic housing
- Recessed label fields
- Accepts front loading snap-in TracJacks
- Front load module approach
- RoHS compliant

### SPECIFICATIONS

#### GENERAL INFO

Color: Stainless steel  
Footprint: TracJack  
Number Of Ports: 4  
Product Series: Clarity  
Type: Plates and Boxes

#### ASSEMBLY/INSTALLATION INFORMATION

Mounting Hardware Included: 6-32 x 1" screws (2 ea)

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: 1  
CUL Listing No: E131600

UL Listing No: E131600

UL Standard: Yes

## CONSTRUCTION INFORMATION

Component 1: Stainless Steel TracJack Faceplate

Component 2: Plastic Backplate

Component 3: Designation Strip

Component 4: Designation Strip

Component 5: Screw 6-32 x 1" flat head

Finish Plating 1: #5 Brushed

Finish Plating 3: Clear

Finish Plating 4: White

Finish Plating 5: Nickel plating 15u"

Material 1: 20 Gauge Stainless Steel

Material 2: PC/ABS UL94-VO

Material 3: Lexan

Material 4: Paper

Material 5: Cold rolled steel 1010

## DIMENSIONS

Depth (Metric): 6.10 mm

Height (Metric): 114.3 mm

Height (US): 4.5"

Width (Metric): 69.85 mm

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: TAIWAN

Buy American Act Status: Trade Agreement Act Compliant