




NOTES, UNLESS OTHERWISE SPECIFIED:

PANDUIT CT-1550 TOOL:

TOOL WEIGHT: 27.2 oz. [77] kg


Crimps most Panduit #22-#10 AWG insulated terminals & splices; and specific insulated disconnects.

Reduced crimp effort advantage for #22-#14 AWG terminations.

Provides UL Listed and CSA Certified terminations with applicable Panduit terminals.

DIMENSIONS SHOWN IN BRACKETS [] ARE METRIC, AND ARE FOR REFERENCE ONLY.

CRIMP POCKET AWG / mm ²	ENGLISH GO / NO GO GAGE MEMBERS		METRIC GO / NO GO GAGE MEMBERS	
	“G” Dia. (GO)	“NG” Dia. (NO GO)	“G” Dia. (GO)	“NG” Dia. (NO GO)
22-14/0,5-2,5	0.101”	0.109”	2,56 mm	2,76 mm
12-10/4,0-6,0	0.147”	0.155”	3,73 mm	3,93 mm

							CT-1550 Contour Crimp™ Crimping Tool CUSTOMER DRAWING						
							ITEM REVISION NAME: TP27602B01_01						
---	---	---	---	---	ADDED GO – NO GO CHART	---	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.x) ± --- (.xxx) ± --- (.xx) ± --- ANGLES ± ---  THIRD ANGLE PROJECTION				MATERIAL: -----		
01	12/12/16	BWG	BJPU	JADE	REMOVED GLOBAL LOGO MOVED MADE IN GERMANY TO FRAME.	4857/ 02					DRAWING NUMBER: TP27602B01		
00	5-07-15	BLR	BJPU	ABJ	RELEASED	4857							
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY: BLR	DATE: 5-07-15	CHK BJPU	SCALE NONE	SHT 1 OF 1	SIZE B	