

## 3U RACK MOUNT FIBER CABINET FOR SPLICE APPLICATIONS

OR-FC03U-S | [Ortronics](#)



### FEATURES & BENEFITS

The 3U (5.25" high) fiber cabinet for splice applications is optimized for integration with the Mighty Mo 6 rack system (OR-MM6710, OR-MM6810 & Seismic Rack OR-MM6710S) with 10.5" channel depth. Each fiber cabinet accepts up to 22 splice trays (264 fibers).



- 19" (483 mm) deep cabinet chassis
- Large cable entry port in rear of cabinet
- Fiber tray slides forward
- Fiber tray slides rearward
- Optimized hook/loop lances embedded in fiber tray
- Comes with patented snap-in fiber management clips
- Large patch cord exit ports at front of cabinet
- Adapter panel face positioned to optimize patch cord management

### SPECIFICATIONS

#### GENERAL INFO

Installation Destination: Rack Mount  
Product Series: OptiMo FC Series

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

#### DIMENSIONS

Depth (Metric): 485.77 mm  
Height (Metric): 133.35 mm  
Height (US): 5.25"  
Width (Metric): 482.60 mm  
Rack Units: 3

## TECHNICAL INFORMATION

Capacity: Standard density  
Equipment Type: Fiber Cabinets

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA  
Buy American Act Status: Buy American Act Compliant

