



4U RACK MOUNT FIBER CABINET FOR COMBINATION PATCH/SPLICE APPLICATIONS

OR-FC04U-C | [Ortronics](#)



FEATURES & BENEFITS

The 4U (7.0" high) fiber cabinet for patch/splice applications is optimized for integration with the Mighty Mo 6 rack system (OR-MM6710, OR-MM6810 & Seismic Rack OR-MM6710S) with 10.5" channel depth. Each fiber cabinet accepts up to 12 adapter panels and 16 splice trays.



- 19" (483 mm) deep cabinet chassis
- Large cable entry port in rear of cabinet
- Fiber tray slides forward
- Fiber tray slides rearward
- Optimized hook/loop lances embedded in fiber tray
- Comes with patented snap-in fiber management clips
- Large patch cord exit ports at front of cabinet
- Adapter panel face positioned to optimize patch cord management

SPECIFICATIONS

GENERAL INFO

Installation Destination: Rack Mount
Product Series: OptiMo FC Series

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

DIMENSIONS

Depth (Metric): 485.77 mm
Height (Metric): 177.80 mm
Height (US): 7"
Width (Metric): 482.60 mm
Rack Units: 4

TECHNICAL INFORMATION

Capacity: Standard density
Equipment Type: Fiber Cabinets

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA
Buy American Act Status: Buy American Act Compliant

