



SURFACE MOUNT FIBER CABINET FOR PATCHING

OR-615SMFC-96P | [Ortronics](#)

FEATURES & BENEFITS

This large volume cabinet accepts our popular Fiber Adapter Panels. The cabinet secures, protects, and organizes single mode or multimode optical terminations. The Cabinet provides interconnect or cross connect facilities between horizontal and backbone inside plant (ISP) or outside plant (OSP) cables. Maximum capacity: 96 Fibers using SC, ST, and FC Adapters, 192 Fibers using MT-RJ and LC Adapters.



- Holds up to 16 adapter panels
- Swing out cross connect panel
- Catching latch closure can be padlocked
- 1.75" openings on top, bottom, and sides
- Easy access design

SPECIFICATIONS

GENERAL INFO

Installation Destination: Surface Mount

ASSEMBLY/INSTALLATION INFORMATION

Mounting Hardware Included: Yes

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

DIMENSIONS

Depth (Metric): 178 mm
Height (Metric): 343 mm
Height (US): 13.5"

Width (Metric): 425 mm

TECHNICAL INFORMATION

Equipment Type: Fiber Cabinets

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant

