

32" Full-HD LCD Monitor



Product Features

- Industrial level DID LCD panel, suitable for extensive 7*24 continuous works.
- Physical resolution of 1920*1080
- High fidelity digital processing, brilliant and vivid video.
- 5ms fast response time, no image ghosting
- Professional thermal design to extend equipment lifespan
- Various of signal input
- Built-in power, low energy consumption, ultra-quiet

Technical Specifications

Model	DHL32-S600	
System		
Diagonal	31.5"(16:9)	
Resolution	1920×1080 (FHD)	
Backlight	LED	
Brightness/Luminance (Standard)	300 cd/m ²	
Contrast	1200:1	
Angle of view	178° /178° (vertical/horizontal)	
Response time	5ms	
Signals		
Input	standard	VGA(D-Sub)×1、HDMI×2、audio input×1 (3.5mm)
	optional	-
Output	Standard	speaker×1
	optional	-
General		
Consumption (Standard)	52W	
Consumption (Standby)	≤0.5W	

Power Supply	AC100~240V (+/-10%),50/60 Hz
Gross Weight	5.4kg
Monitor dimensions	731.2mm × 468.9mm × 186.3mm
Work Environment	Temperature: 0℃~40℃
	Humidity: 10%~90%
Accessory	
Standard	VGA cable, power cable, HDMI cable
Optional	Pedestal, hanging bracket

*Design and specifications are subject to change without notice.

Dimensions(mm)

