

AL62412CX

Linear Power Supply/Charger Kit

Description

Altronix AL62412CX linear power supply/charger kit has a wide range of applications including access control, security, and CCTV system accessories that require additional power. Kit includes: AL624 power supply, 12VDC/7AH rechargeable battery, and 16.5VAC 20VA Class 2 Rated plug-in transformer.



AL62412CX

Specifications

Input

Voltage 115VAC, 60 Hz, 1.2A.

Output

Voltage 12VDC.

Current 1.2A supply current.

Other Short circuit and thermal overload protection.
Filtered and regulated.

Back-up Battery *(not included)*

Type Sealed lead acid or gel type.

Failover Upon AC loss, instantaneous.

Indicators (LED)

Input Input voltage is present.

DC Output Powered.

Physical and Environmental

Board Dimensions (L x W x H)

2.5" x 3" x 1.5" (63.5mm x 76.2mm x 38.1mm).

Product Weight 5.5 lbs. (2.5 kg).

Shipping Weight 6.3 lbs. (2.76 kg).

Temperature

Operating 0°C to 49°C (32°F to 120°F).

Storage -20°C to 70°C (-4°F to 158°F).

Relative Humidity 85% +/-5%.

BTU/Hr. (approx.): 7 BTU/Hr.