

T2428175220

Open Frame Transformer

Description

Altronix T2428175220 open frame transformer provides power for electronic power supplies and equipment including security, access control, and surveillance devices.



T2428175220

Specifications

Input

Voltage 220VAC, 50/60 Hz, 0.8A.

Outputs

Voltage 24VAC/175VA or 28VAC/175VA.

Current 7.25A @ 24VAC or 6.25A @ 28VAC.

Physical and Environmental

Please see the drawing below for dimensions.

Product Weight 7.3 lbs. (3.31 kg).

Shipping Weight 8.05 lbs. (3.65 kg).

Temperature

Operating 0°C to 49°C (32°F to 120°F).

Storage -20°C to 70°C (-4°F to 158°F).

Relative Humidity 85% +/-5%.

BTU/Hr. (approx.): 90 BTU/Hr.

Transformer Drawing and Dimensions

