

VertiLine16 CCTV Rack Mount Power Supply

Description

Altronix VertiLine16 CCTV Rack Mount Power Supply provides sixteen (16) fuse protected power outputs in a space saving 1U EIA 19" rack mount chassis which may be rack, wall or shelf mounted. This unit features individually selectable 24VAC and/ or 28VAC power outputs with surge suppression.



VertiLine16

Specifications

Input

Voltage 115VAC, 60 Hz, 3A or
230VAC, 50/60 Hz, 1.5A.

Output

Sixteen (16) individually selectable power outputs with OFF position.

Voltage 24VAC or 28VAC.

Current 10A max. total supply current.

Fusing Individual outputs' fuses rated @ 3A.
Main fuse rated @ 10A.

Other Short circuit and thermal overload protection.
Filtered and regulated.

Indicators (LED)

Master Illuminated master power disconnect
circuit breaker with manual reset.

Output Sixteen (16) individual LEDs.

Agency Listings

UL UL2044 (Commercial CCTV Equipment).
CE European Conformity.
C-Tick compliant.

Physical and Environmental

Dimensions (H x W x D)

1.625" x 19.125" x 8.5" (41.3mm x 486mm x 216mm).

Product Weight 12.15 lbs. (5.51 kg).

Shipping Weight 13.45 lbs. (6.1 kg).

Temperature

Operating 0°C to 49°C (32°F to 120°F).

Storage -20°C to 70°C (-4°F to 158°F).

Relative Humidity 85% +/-5%.

BTU/Hr. (approx.):

24VAC: 123 BTU/Hr.

28VAC: 143 BTU/Hr.