

VertiLine63DV -**Rack Mount DC Power Supply**

Description

Altronix Vertiline63DV Rack Mount DC Power Supply provides sixteen (16) filtered and electronically regulated auto-resettable power outputs in a space saving 1U EIA 19" rack mount chassis.

 Specifications 			
Input		Agency Listings	
Voltage	220VAC, 50/60Hz, 1.5A.	CE European Conformity.	
Output		Physical and Environmental	
Voltage	24VDC.	Dimensions (H x W x D)	
Current	8A max. total supply currect.	1.625" x 19.125" x 8.5" (41.3mm x 486mm x 216mm).	
Fusing	Individual outputs' PTCs rated @ 2.5A.	Product Weight 7.2 lbs. (3.27 kg).	
Other	Short circuit and thermal overload protection.	Shipping Weight 8.3 lbs. (3.76 kg). Temperature	
	Filtered and regulated.		
		Operating	0°C to 49°C (32°F to 120°F).
Indicators (LED)		Storage	-20°C to 70°C (-4°F to 158°F).
Master	Illuminated master power disconnect	Relative Humidity	85% +/-5%.
	circuit breaker with manual reset.	BTU/Hr. (approx.):	98 BTU/Hr.
Output	Sixteen (16) individual LEDs.		

Altronix Corporation | 140 58th St | Brooklyn, NY 11220 USA phone: +1 718.567.8181 | fax: +1 718.567.9056 | email: info@altronix.com | www.altronix.com





Rev. VertiLine63DV-05252017