

## WayPoint307A Outdoor AC Power Supply/Charger

### Description

Altronix WayPoint307A Outdoor Power Supply provides 24VAC and/or 28VAC distributed via two outputs for powering CCTV cameras, heaters, and other video accessories. It is designed to be conveniently located where power is required. Lightweight molded fiberglass reinforced polyester enclosure is NEMA 4/4X, IP66-11 Rated for outdoor use. It features lockable stainless steel latches and integral flanges to simplify wall or pole mounting.



WayPoint307A

### Specifications

#### Input

Voltage 277VAC, 60Hz, 1.75A.

#### Output Options

- a. 24VAC @ 12.5A max.
- b. 28VAC @ 10A max.
- c. Both 24VAC and 28VAC, not to exceed 10A max.

Fuse Ratings 15A / 250V.

#### Indicators (LED)

Input Input voltage is present.  
DC Output Powered.

#### Agency Listings

CE European Conformity

#### Physical and Environmental

##### Dimensions (H x W x D)

13.31" x 11.31" x 5.59" (338.1mm x 287.3mm x 142mm).

Product Weight 15.45 lbs. (7.01 kg).

Shipping Weight 16.75 lbs. (7.6 kg).

##### Temperature

Operating -20°C to 50°C (-4°F to 122°F).

Storage -40°C to 70°C (-40°F to 158°F).

Relative Humidity 85% +/-5%.

BTU/Hr. (approx.): 154 BTU/Hr.

### Accessories

PMK1 Pole Mount Kit (order separately)

PMK1 pole mount kit is designed to simplify installation of outdoor units.

It accommodates 2" - 8" (diameter) poles.

Kit includes:

- Two (2) powder coated steel mount brackets.
- Four (4) stainless steel bolts.
- Four (4) stainless steel lock washers.
- Two (2) wormgear quick release straps.



PMK1