

# JABRA SPEAK™ 810

Conference Calls Made Simple; Collaboration Made Easy



Works with any *Bluetooth* enabled device

- Intended for 15 meeting room attendees
- Unique ZoomTalk™ Microphones
- USB charge out port



FEATURE	BENEFIT
Packaging dimensions	H 456 x L 287 x W 366 mm
Weight mono / duo	965g (1570g include packaging)
Whats in the box	Jabra SPEAK 810, Charger (incl. PE bag), Exchangeable pins (4 pcs), Warning leaflet, Warranty leaflet, Quick Start Guide, Korean leaflet, Foam bag, Tape, Silica bag
Battery included	No
AC power supply	Yes
Certifications	Regulatory Approvals: CE, FCC, IC, EAC, RRC, CCC, RCM, KCC, TELEC, iDA, NCC, RoHS, REACH, ETA, SIRIM, SDPPI, RCM, NTC Industrial Certifications: Bluetooth 4.1, Skype for Business, Cisco, Avaya, Mitel, Alcatel, Unify
Warranty	2 years
Bluetooth device	Yes
DECT Device	No
NFC	Yes
Operating range	Up to 30m/100ft
Headset bandwidth	Wideband
Connection (mini jack, USB, etc)	USB/Bluetooth/3.5 mm jack
What is Bluetooth wireless technology	Bluetooth version 4.1
Speaker Size	L 56 x W 56 x H 28mm
Speaker sensitivity	80±2dB@1W/1m
Speaker impedance	4 ohm
Speaker Max Input Power	6W
Speaker Frequency Range	100Hz – 20KHz
Microphone type	Digital MEMS, bottom port
Microphone Sensitivity	VDD=1.8V, FCLK =2.4MHz, (0dBFS2=1V/Pa@1kHz), Min-29dB, Normak: -26dB, Max -23dB
Microphone Frequency Range	20Hz – 8K Hz
Supported Bluetooth profiles	A2DP (v1.2), Hands Free Profile (v1.6), Headset Profile (v1.2), AGHFP (v1.6)
Bluetooth wireless technology	Bluetooth 4.1
Speaker bandwidth Music mode	HiFi
Speaker bandwidth Speak mode	Wideband
Microphone bandwidth	Wideband
Cord length	USB Cord Length: 2.1 m, 3.5mm jack Cord length 1.2m
Operating temperature	-10 °C to + 50 °C
Storage temperature	-30 °C to + 80 °C Storage temperature range: (-20°C to +35°C 6 months), (+35°C to +45°C 3 months), (+45°C to +45°C 1 month), (+60°C to +70°C 1 hour with no degradation), (+70°C to +85°C max. 1 hour (<20% degradation)
Supported modes	SCO, eSCO, Sniff mode
Security	Pairing, Authentication and Encryption (Bluetooth standard)
Paired devices	Up to 900 trusted devices
Power consumption speaker	6W
Features	ZoomTalk™ microphone with adaptive array 5 m/15 ft. range (15 persons), Microphone focus (zoom on the person speaking) Connectivity: USB, BT/NFC & 3.5mm jack (AUX), USB charge out for tablets and mobile phones, Kensington lock slot, Intuitive on-device call-controls and indicators for true UC experience, Plug & play for all smart device and all communication platforms

SKU	DESCRIPTION	EAN CODE
7810-109	Jabra SPEAK 810 MS	5706991018448
7810-209	Jabra SPEAK 810 UC	5706991019308
7810-199	Jabra SPEAK 810 MS	5706991019308
7810-299	Jabra SPEAK 810 UC	5706991019315